

151-30001

HellermannTyton



Article Number: 151-30001

Description: Masonry Cable Tie Mount, 1.24" Long, .25" Hole Dia, .18" Max Cable Tie Width, PA46, Black, 1000/pkg

Base Data		
	Local Order Number	MMB.50M4
	Type	MMB.5
	Color	Black (BK)
	Features and benefits	• Masonry Mounts provides a permanent solution when fastening wire and cables to masonry surfaces. • The mounts have easy installation into predrilled holes allowing for faster use.
	Quantity Per	bag
	Product Description	HellermannTyton masonry mounts provide a permanent mounting solution when fastening wire and cables to masonry surfaces. Designed for easy installation by simply tapping into predrilled holes.
	Short Description	Masonry Cable Tie Mount, 1.24" Long, .25" Hole Dia, .18" Max Cable Tie Width, PA46, Black, 1000/pkg
Product Dimensions		
	Length L (Imperial)	1.24"
	Length L (Metric)	31.5mm
	Fixation Method	with Fir Tree (Mounts)
	Width W (Imperial)	0.375"
	Width W (Metric)	9.5mm
	Cable Tie Width Max. (Imperial)	0.18"
	Cable Tie Width Max. (Metric)	4.6mm
	Width W2 (Imperial)	0.22"
	Width W2 (Metric)	5.6mm
	Width W3 (Imperial)	0.308"
	Width W3 (Metric)	7.8mm
	Height H (Imperial)	.37"
	Height H (Metric)	9.40mm
	Mounting Hole Diameter D (Imperial)	0.25"
	Mounting Hole Diameter D (Metric)	6.35 mm

151-30001



Material and Specifications		
	Material	Polyamide 4.6 (PA46)
	Material Shortcut	PA46
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +275°F (-40°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987