

154-00013

HellermannTyton

Article Number: 154-00013



Description: Flat Ribbon Clamp, Adhesive Mount, 1.2" Max Cable Width, .156" Hole Dia, PA66, Gray, 50/pkg

Base Data		
	Local Order Number	FC1.2AK2
	Type	FC1.2A
	Color	Gray (GY)
	Features and benefits	<ul style="list-style-type: none"> • Adjustable height feature allows the clamp to close to the exact height of the ribbon cable. • Releasable for easy access to cables when necessary. • Available in adhesive or screw mount versions.
	Quantity Per	bag
	Product Description	HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary. These clamps are available in adhesive or screw mount versions.
	Short Description	Flat Ribbon Clamp, Adhesive Mount, 1.2" Max Cable Width, .156" Hole Dia, PA66, Gray, 50/pkg
Product Dimensions		
	Length L (Imperial)	0.75"
	Length L (Metric)	19.0mm
	Width W (Imperial)	1.5"
	Width W (Metric)	38.1mm
	Height H (Imperial)	.50"
	Height H (Metric)	12.70mm
	Mounting Hole Diameter D (Imperial)	0.156"
	Mounting Hole Diameter D (Metric)	4.0 mm
	For Cable Width Max. (Metric)	30.48mm
	For Cable Width Max. (Imperial)	1.2"

154-00013



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Adhesive	Acrylate with base of polyurethane foam
	Adhesive Operating Temperature	to +230°F (+110°C)
	Flammability	UL 94 V2 (excluding adhesive)
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50Pieces
	Customs Number(Schedule B)	3926909987