

155-05400

HellermannTyton

Article Number: 155-05400

Description: Oval Stud Mount Cable Tie, Designed for 5.0 mm stud, 6.0" Long, PA66HS, Black, 500/pkg



Base Data		
	Local Order Number	155-05400
	Type	T50SOSSB5HEC
	Color	Black (BK)
	Features and benefits	• Oval mount design pushes on easy by hand without the need for tools. • Design provides low insertion and high extraction force.
	Quantity Per	bag
	Product Description	The special oval shape provides for an approximate .20" (5.0 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect positioning of the tie on the cables
	Short Description	Oval Stud Mount Cable Tie, Designed for 5.0 mm stud, 6.0" Long, PA66HS, Black, 500/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	170N
	Length L (Imperial)	6.0"
	Length L (Metric)	160mm
	Fixation Method	Weld Stud Fixing
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Outside Serrated
	Width W (Imperial)	0.19"
	Width W (Metric)	4.6mm
	Height H2 (Imperial)	0.63"
	Bundle Diameter Min. (Imperial)	0.04"
	Bundle Diameter Min. (Metric)	1.0mm
	Bundle Diameter Max. (Imperial)	1.4"

155-05400



Product Dimensions	Bundle Diameter Max. (Metric)	35.0mm
	Stud Length min (metric)	11.0mm
	Stud Length Max. (Imperial)	0.63"
	Stud Length Max. (Metric)	16.0mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.35mm
	Stud Diameter (Imperial)	0.2"
	Stud Diameter (Metric)	5.0 mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	2.75kg