

156-00291

HellermannTyton



Article Number: 156-00291

Description: 2-Piece Cable Tie/Fir Tree Mount, 8.0"L, .26"—.28"
Mounting Hole, 30lb, PA66HS, Black, 500/pkg

Base Data		
	Local Order Number	156-00291
	Type	T50RFT7
	Color	Black (BK)
	Features and benefits	• Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation. • Initial fir tree serves as a locating feature for assistance in blind assembly applications. • Disc feature provides anti-rattle protection in high vibration applications.
	Quantity Per	bag
	Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole and protect against dirt and other impurities. The mount can slide along the strap of the cable tie for proper orientation. The fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
	Short Description	2-Piece Cable Tie/Fir Tree Mount, 8.0"L, .26"—.28" Mounting Hole, 30lb, PA66HS, Black, 500/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	8.0"
	Length L (Metric)	203.2mm
	Length L2 (Imperial)	0.5"
	Length L3 (Imperial)	0.8"
	Length L3 (metric)	18.6mm
	Fixation Method	Fir Tree
	Identification Plate Position	none
	Length L2 (Metric)	12.0mm
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated

156-00291



Product Dimensions	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm
	Width W2 (Imperial)	0.5"
	Width W2 (Metric)	11.6mm
	Width W3 (Imperial)	0.2"
	Width W3 (Metric)	5.0mm
	Height H (Imperial)	.05"
	Height H (Metric)	1.20mm
	Height H2 (Imperial)	.50"
	Height H2 (Metric)	12.70mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.8"
	Bundle Diameter Max. (Metric)	50.0mm
	Disc Diameter (Imperial)	0.63"
	Disc Diameter (Metric)	16.0mm
	Panel Thickness Max. (Imperial)	0.28"
	Panel Thickness Max. (Metric)	7.0mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.8mm
	Mounting Hole Diameter D (Imperial)	0.26 - 0.28"
	Mounting Hole Diameter D (Metric)	6.5 - 7.0 mm
	Mounting Hole Diameter D Max. (Imperial)	0.8"
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987