

156-00444

HellermannTyton

Article Number: 156-00444

Description: Arrowhead Push Mount Tie with Seal, 8.5" Long, 50lb, Bundle Max 2.0", PA66HIRHS, Natural, 500/bag



Base Data		
	Local Order Number	156-00444
	Type	T50ROSAH6MDU
	Color	Natural (NA)
	Features and benefits	<ul style="list-style-type: none"> • The arrowhead design of this tie offers a positive, low insertion force and a high extraction force. • Tie features a foam rubber seal which provides additional protection against moisture, dirt and other impurities.
	Quantity Per	bag
	Product Description	The Arrowhead Mount Tie with seal provides a strong extraction force while being able to seal holes with it's foam rubber seal which helps prevent against dirt and other impurities. This is used in many markets such as automobiles, aircrafts, and washing machines.
	Short Description	Arrowhead Push Mount Tie with Seal, 8.5" Long, 50lb, Bundle Max 2.0", PA66HIRHS, Natural, 500/bag
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	8.5"
	Length L (Metric)	216.0mm
	Fixation Method	Arrowhead
	Identification Plate Position	none
	Tie Closure	plastic pawl
	Variant	Outside Serrated
	Width W (Imperial)	0.2"
	Width W (Metric)	5.0mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.6mm
	Bundle Diameter Max. (Imperial)	2.0"
	Bundle Diameter Max. (Metric)	50.0mm

156-00444



Product Dimensions	Disc Diameter (Imperial)	0.63"
	Disc Diameter (Metric)	16.0mm
	Panel Thickness Max. (Imperial)	0.08"
	Panel Thickness Max. (Metric)	2.1mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.8mm
	Mounting Hole Diameter D (Metric)	6.2 - 6.6 mm
	Mounting Hole Diameter D Min. (Imperial)	0.248"
	Mounting Hole Diameter D Max. (Imperial)	0.252"
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987