

156-00457

HellermannTyton



Article Number: 156-00457

Description: Heavy-Duty Fir Tree Mount Cable Tie, 8" x .18", .03"—.28", Panel Thickness, PA46, Brown, 500/pkg

Base Data		
	Local Order Number	156-00457
	Type	T50RFT7HD
	Color	Brown (BN)
	Features and benefits	• Staggered fir tree branch design provides low insertion forces and high extraction forces. • Initial fir tree serves as a locating feature for assistance in blind assembly applications. • Disc feature provides anti-rattle protection in high vibration applications.
	Quantity Per	bag
	Product Description	Heavy Duty fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie, and is ideal in heavy duty environments.
	Short Description	Heavy-Duty Fir Tree Mount Cable Tie, 8" x .18", .03"—.28", Panel Thickness, PA46, Brown, 500/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	8.0"
	Length L (Metric)	200.0mm
	Length L2 (Imperial)	0.5"
	Length L3 (imperial)	0.78"
	Length L3 (metric)	19.3mm
	Fixation Method	Fir Tree
	Identification Plate Position	none
	Length L2 (Metric)	11.6mm
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.18"

156-00457



Product Dimensions	Width W (Metric)	4.6mm
	Width W2 (Imperial)	0.23"
	Width W2 (Metric)	5.9mm
	Width W3 (Imperial)	0.23"
	Width W3 (Metric)	5.9mm
	Height H (Imperial)	.78"
	Height H (Metric)	19.80mm
	Height H2 (Imperial)	.36"
	Height H2 (Metric)	9.14mm
	Bundle Diameter Min. (Imperial)	0.16"
	Bundle Diameter Min. (Metric)	4.0mm
	Bundle Diameter Max. (Imperial)	1.8"
	Bundle Diameter Max. (Metric)	45.0mm
	Disc Diameter (Imperial)	0.9"
	Disc Diameter (Metric)	21.6mm
	Panel Thickness Max. (Imperial)	0.28"
	Panel Thickness Max. (Metric)	7.0mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.8mm
	Mounting Hole Diameter D (Imperial)	0.24 - 0.28"
	Mounting Hole Diameter D (Metric)	6.2 - 7.2 mm
	Mounting Hole Diameter D Min. (Imperial)	0.244"
	Mounting Hole Diameter D Max. (Imperial)	0.284"
Material and Specifications		
	Material	Polyamide 4.6 (PA46)
	Material Shortcut	PA46
	Material Cable Tie	Polyamide 4.6 (PA46)
	Flammability	UL 94 V2
	Operating Temperature	+275°F (+135°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500

156-00457



Logistic and Packaging	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces