

156-00940

HellermannTyton



Article Number: 156-00940

Description: Cable Tie & Edge Clip, 8.0" Long, EC4A, Panel Thickness .04"-.12", 50lb, PA66, Natural, 500/bag

Base Data		
	Local Order Number	156-00940
	Type	T50REC4B
	Color	Natural (NA)
	Features and benefits	• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments. • Two piece assembly allows the mount to slide along the strap ensuring proper orientation. • Cable tie is outside serrated to reduce bundle chafing.
	Quantity Per	bag
	Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
	Short Description	Cable Tie & Edge Clip, 8.0" Long, EC4A, Panel Thickness .04"-.12", 50lb, PA66, Natural, 500/bag
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	8.0"
	Length L (Metric)	200.0mm
	Length L2 (Imperial)	0.6"
	Fixation Method	EdgeClip, top, assembled, 2 piece
	Identification Plate Position	none
	Length L2 (Metric)	14.0mm
	Releasable Closure	No
	Variant	Inside Serrated
	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm

156-00940



Product Dimensions	Width W2 (Imperial)	0.5"
	Width W2 (Metric)	11.5mm
	Height H (Imperial)	.05"
	Height H (Metric)	1.20mm
	Height H2 (Imperial)	.40"
	Height H2 (Metric)	10.16mm
	Bundle Diameter Min. (Imperial)	0.2"
	Bundle Diameter Min. (Metric)	4.0mm
	Bundle Diameter Max. (Imperial)	2.0"
	Bundle Diameter Max. (Metric)	50.0mm
	Panel Thickness Max. (Imperial)	0.12"
	Panel Thickness Max. (Metric)	3.0mm
	Panel Thickness Min. (Imperial)	0.04"
	Panel Thickness Min. (Metric)	1.0mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987