

156-01092

# HellermannTyton



Article Number: 156-01092

Description: Locking Omega Clip, 10–14mm, Unassembled with T50R, PA66HIRHS, Black, 2000/ctn

Base Data		
	Local Order Number	156-01092
	Type	T50RLOC10-14-SET
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• The 360 degree enclosure ensures the entire bundle is secure when being routed by this clip.</li> <li>• Locking tab on this clip is small enough that it will not interfere with any other portion of the wire routing, but is significant enough to allow for manual disengagement if service is needed.</li> <li>• The cable tie portion of this two-piece design allows for two wire bundles to be routed with the same piece.</li> </ul>
	Quantity Per	box
	Product Description	HellermannTyton's two-piece cable tie assembly offers dual bundle routing. The omega clip portion creates a full and secure lock completely around one bundle, while the cable tie creates a secure solution for a second bundle.
	Short Description	Locking Omega Clip, 10–14mm, Unassembled with T50R, PA66HIRHS, Black, 2000/ctn
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	220.0N
	Length L (Imperial)	1.72"
	Length L (Metric)	43.73mm
	Fixation Method	Omega Clips
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.47"
	Width W (Metric)	12.0mm
	Bundle Diameter Min. (Imperial)	0.39"
	Bundle Diameter Min. (Metric)	10.0mm

156-01092

**HellermannTyton**

Product Dimensions	Bundle Diameter Max. (Imperial)	0.55"
	Bundle Diameter Max. (Metric)	14.0mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	2000
	Package Quantity (Metric)	2000
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces