

156-01345



Article Number: 156-01345

Description: Omega Clip Cable Tie, 6.0" Long, Attaches to Diameter 1.2" - 1.5", PA66HS, Black, 250/pkg



Base Data		
	Local Order Number	156-01345
	Type	T50SVCOC31-39
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Omega Clip can be turned 360 degrees allowing for orientation in any direction.</li> <li>• Design allows quick and easy installation by hand without the need for tools.</li> <li>• Multiple bundle diameters available for all different ranges of bundles.</li> </ul>
	Quantity Per	carton
	Product Description	Omega Clip Cable Ties provide the opportunity to attach a wire or hose to an existing bundle. Offering a full range of orientations, the wire/hose can be orientated in any direction in relations to the main harness. The Omega Clip design is ideally suited for easing the application process on the production floor by allowing for an easy one-step snap fit of the harness assembly to the wire or hose
	Short Description	Omega Clip Cable Tie, 6.0" Long, Attaches to Diameter 1.2" - 1.5", PA66HS, Black, 250/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	222N
	Length L (Imperial)	6.1"
	Length L (Metric)	155mm
	Fixation Method	Omega Clips
	Identification Plate Position	none
	Tie Closure	plastic pawl
	Width W (Imperial)	0.19"
	Width W (Metric)	4.7mm
	Bundle Diameter Min. (Imperial)	0.079"
	Bundle Diameter Min. (Metric)	2.0mm
	Bundle Diameter Max. (Imperial)	1.38"
	Bundle Diameter Max. (Metric)	35.0mm
	Thickness T (Metric)	1.35mm

156-01345



Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	250
	Package Quantity (Metric)	250Bag
	Customs Number(Schedule B)	3926909987