

157-00001

HellermannTyton

Article Number: 157-00001

Description: Fir Tree Mount Cable Tie, 8.3" Long, .25"-.28" Mounting Hole, 50lb, PA66HS, Black, 1000/pkg



Base Data	
Local Order Number	T50RTM25E0HSM4
Type	T50RTM25E
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation. • Initial fir tree serves as a locating feature for assistance in blind assembly applications. • Disc feature provides anti-rattle protection in high vibration applications.
Quantity Per	bag
Product Description	Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.
Short Description	Fir Tree Mount Cable Tie, 8.3" Long, .25"-.28" Mounting Hole, 50lb, PA66HS, Black, 1000/pkg
Product Dimensions	
Minimum Tensile Strength (Imperial)	50.0lbs
Minimum Tensile Strength (Metric)	222N
Length L (Imperial)	8.0"
Length L (Metric)	213.8mm
Fixation Method	Fir Tree
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19"
Width W (Metric)	4.7mm
Bundle Diameter Min. (Imperial)	0.06"
Bundle Diameter Min. (Metric)	1.6mm

157-00001



Product Dimensions	Bundle Diameter Max. (Imperial)	2.0"
	Bundle Diameter Max. (Metric)	50.8mm
	Disc Diameter (Imperial)	0.5"
	Disc Diameter (Metric)	12.6mm
	Panel Thickness Max. (Imperial)	0.5"
	Panel Thickness Max. (Metric)	13.9mm
	Panel Thickness Min. (Imperial)	0.09"
	Panel Thickness Min. (Metric)	2.3mm
	Mounting Hole Diameter D (Imperial)	0.28"
	Mounting Hole Diameter D (Metric)	6.25 - 7.0 mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987