

161-05030

HellermannTyton



Article Number: 161-05030

Description: Spiralwrap Protective Sheathing, .25" Diameter, PE-FR, Natural, 100 ft/roll

Base Data		
	Local Order Number	2FRP9C
	Type	2FRP
	Color	Natural (NA)
	Features and benefits	• Sheathing allows flexible routing and lead-out of cables • The inner edges are beveled preventing damage to cables • Sheathing is reusable and resistant to most chemicals • Spiralwrap is U.L. Recognized
	Quantity Per	reel
	Product Description	HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
	Short Description	Spiralwrap Protective Sheathing, .25" Diameter, PE-FR, Natural, 100 ft/roll
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Variant	Spiral Binding
	Bundle Diameter Min. (Imperial)	0.18"
	Bundle Diameter Min. (Metric)	4.75mm
	Bundle Diameter Max. (Imperial)	2.0"
	Bundle Diameter Max. (Metric)	50.8mm
	Diameter D (imperial)	0.25"
	Diameter D (metric)	6.35mm
	Nominal Diameter (Imperial)	1/4"
	Nominal Diameter (Metric)	6.35mm
	Wall Thickness WT (Imperial)	.045"
	Wall Thickness WT (Metric)	1.14mm

161-05030

HellermannTyton

Product Dimensions	Pitch (imperial)	0.375"
	Pitch (metric)	9.53mm
Material and Specifications		
	Material	Polyethylene, flame retardant (PE-FR)
	Material Shortcut	PE-FR
	Flammability	UL 94 V0
	Operating Temperature	-4°F to +176°F (-20°C to +80°C)
	ROHS Compliant	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987