

161-63303

HellermannTyton



Article Number: 161-63303

Description: Helawrap, HWPAV020, 3/4" (20mm) Dia, PA6V0, Black, 100 ft/reel

Base Data		
	Local Order Number	161-63303
	Type	HWPAV020
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Designed for applications that demand high flame retardant materials • Unique open design allows for easy branch-offs at any point along the harness • Overwrap formation provides abrasion protection and accommodates multiple bundle configurations • Flexible construction and design is well suited for applications that involve movement and vibration • Easy-to-use installation tool makes assembly fast and easy
	Quantity Per	reel
	Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.
	Short Description	Helawrap, HWPAV020, 3/4" (20mm) Dia, PA6V0, Black, 100 ft/reel
Product Dimensions		
	Length L (Imperial)	100.0ft
	Length L (Metric)	30.48m
	Reel Length (imperial)	100.0ft
	Variant	Spiral Binding
	Bundle Diameter Min. (Imperial)	0.71"
	Bundle Diameter Min. (Metric)	18mm
	Bundle Diameter Max. (Imperial)	0.83"
	Bundle Diameter Max. (Metric)	21mm
	Diameter D (imperial)	0.75"
	Diameter D (metric)	20.0mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	20.0mm

161-63303

HellermannTyton

Product Dimensions	Wall Thickness WT (Imperial)	0.037"
	Wall Thickness WT (Metric)	0.95mm
	Pitch (imperial)	0.63"
	Pitch (metric)	16.0mm
Material and Specifications		
	Material	Polyamide 6 V0 (PA6V0)
	Material Shortcut	PA6V0
	Flammability	UL 94 V0
	Halogenfree	Yes
	Operating Temperature	-40°F to +194°F (-40°C to +90°C)
	ROHS Compliant	Yes
	Certification/Specification	UL UL 1441
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100ft
	Package Quantity (Metric)	30.48m
	Customs Number(Schedule B)	3926909987
	Weight (imperial)	5.73lbs
	Weight (Metric)	2.6kg