

161-64216

HellermannTyton



Article Number: 161-64216

Description: Helawrap, HWPP16, 5/8" (16mm) Dia, PP, White, 100 ft/reel

| | | |
|--------------------|---------------------------------|--|
| Base Data | | |
| | Local Order Number | 161-64216 |
| | Type | HWPP16 |
| | Color | White (WH) |
| | Features and benefits | <ul style="list-style-type: none"> • Unique open design for easy branch-offs at any point along the harness. • Overwrap formation provides abrasion protection and accommodates multiple bundle configurations. • Flexible construction and design eliminates pinch points and minimizes bending fatigue, making it ideal for applications involving movement and vibration. • Split shape allows for future access without disassembly. |
| | Quantity Per | reel |
| | Product Description | The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations. |
| | Short Description | Helawrap, HWPP16, 5/8" (16mm) Dia, PP, White, 100 ft/reel |
| Product Dimensions | | |
| | Length L (Imperial) | 100.0ft |
| | Length L (Metric) | 30.48m |
| | Reel Length (imperial) | 100.0ft |
| | Variant | Spiral Binding |
| | Bundle Diameter Min. (Imperial) | 0.51" |
| | Bundle Diameter Min. (Metric) | 12.95mm |
| | Bundle Diameter Max. (Imperial) | 0.63" |
| | Bundle Diameter Max. (Metric) | 16.0mm |
| | Diameter D (imperial) | 0.5" |
| | Diameter D (metric) | 12.70mm |
| | Nominal Diameter (Imperial) | 5/8" |
| | Nominal Diameter (Metric) | 16.0mm |

161-64216

HellermannTyton

| | | |
|-----------------------------|------------------------------|-----------------------------------|
| Product Dimensions | Wall Thickness WT (Imperial) | 0.03" |
| | Wall Thickness WT (Metric) | 0.8mm |
| | Pitch (imperial) | 0.51" |
| | Pitch (metric) | 12.95mm |
| Material and Specifications | | |
| | Material | Polypropylene (PP) |
| | Material Shortcut | PP |
| | Flammability | UL 94 HB |
| | Halogenfree | Yes |
| | Operating Temperature | -76°F to +230°F (-60°C to +110°C) |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 100ft |
| | Package Quantity (Metric) | 30.48m |
| | Customs Number(Schedule B) | 3926909987 |
| | Weight (imperial) | 2.55lbs |
| | Weight (Metric) | 1.16kg |