

166-11808

# HellermannTyton



Article Number: 166-11808

Description: HelaGuard Non-Metallic Conduit, Double Slit, Std Wt, 0.38" Dia, Nylon PA6, Black, 164 ft/Std. Reel

Base Data		
	Local Order Number	166-11808
	Type	HG-DC0380
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Double slit opening offers easy access during installation and maintenance.</li> <li>• Material is easy to use and cut; reduces installation time and labor costs.</li> <li>• Flexible, abrasion resistant and durable for a variety of applications.</li> <li>• Good impact strength; recovers quickly if crushed.</li> <li>• UV resistant; suitable for use in outdoor applications.</li> <li>• Offered in fine or course corrugated pitch.</li> </ul>
	Product Description	A standard weight corrugated conduit with two slit openings that eases installation and maintenance of wire and cable bundles. The interlocking construction is excellent for retrofitting projects. PA6 material is highly resistant to solvents and oils, and offers UV and abrasion resistance.
	Short Description	HelaGuard Non-Metallic Conduit, Double Slit, Std Wt, 0.38" Dia, Nylon PA6, Black, 164 ft/Std. Reel
Product Dimensions		
	Length L (Imperial)	164.0ft
	Length L (Metric)	50m
	Inner Diameter D (Imperial)	0.41"
	Inner Diameter ID (metric)	10.3mm
	Euro (NW) Size	12mm
	Pitch Type	F (Fine)
	Trade Size	3/8 "
	Outside Diameter D (imperial)	0.63"
	Outside Diameter OD (metric)	15.8mm
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	16mm
	Inside Bend Radius (Imperial)	3.94"
	Inside Bend Radius (Metric)	100mm

166-11808



Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	PA6
	Flammability	Self-Extinguishing according to EN IEC 61386
	Halogenfree	Yes
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	164ft
	Package Quantity (Metric)	50m
	Customs Number(Schedule B)	3926909987