

166-11812

HellermannTyton



Article Number: 166-11812

Description: HelaGuard Non-Metallic Conduit, Double Slit, Std Wt, 1.25" Dia, Nylon PA6, Black, 82 ft/Std. Reel

Base Data		
	Local Order Number	166-11812
	Type	HG-DC1250
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Double slit opening offers easy access during installation and maintenance. • Material is easy to use and cut; reduces installation time and labor costs. • Flexible, abrasion resistant and durable for a variety of applications. • Good impact strength; recovers quickly if crushed. • UV resistant; suitable for use in outdoor applications. • Offered in fine or coarse corrugated pitch.
	Product Description	A standard weight corrugated conduit with two slit openings that eases installation and maintenance of wire and cable bundles. The interlocking construction is excellent for retrofitting projects. PA6 material is highly resistant to solvents and oils, and offers UV and abrasion resistance.
	Short Description	HelaGuard Non-Metallic Conduit, Double Slit, Std Wt, 1.25" Dia, Nylon PA6, Black, 82 ft/Std. Reel
Product Dimensions		
	Length L (Imperial)	82.0ft
	Length L (Metric)	25m
	Inner Diameter D (Imperial)	1.26"
	Inner Diameter ID (metric)	32mm
	Euro (NW) Size	36mm
	Pitch Type	C (Coarse)
	Trade Size	1-1/4 "
	Outside Diameter D (imperial)	1.68"
	Outside Diameter OD (metric)	42.5mm
	Nominal Diameter (Imperial)	1-1/4"
	Nominal Diameter (Metric)	42mm
	Inside Bend Radius (Imperial)	7.88"
	Inside Bend Radius (Metric)	200mm

166-11812



Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	PA6
	Flammability	Self-Extinguishing according to EN IEC 61386
	Halogenfree	Yes
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25m
	Customs Number(Schedule B)	3926909987