

166-50174

HellermannTyton



Article Number: 166-50174

Description: HelaGuard Metal Locknuts, Metric Thread, 40mm, Nickel Plated Brass, Silver, 1/pkg

Base Data		
	Local Order Number	166-50174
	Type	ALNPB-M40
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> • Nickel plated brass thread ensures secure connection with brass plated fittings. • Metric thread pattern works with metric thread fittings.
	Quantity Per	bag
	Product Description	Locknuts work with metric threaded fittings or knockout entries.
	Short Description	HelaGuard Metal Locknuts, Metric Thread, 40mm, Nickel Plated Brass, Silver, 1/pkg
Product Dimensions		
	Wrenching Flat Size (Imperial)	1.89"
	Wrenching Flat Size (Metric)	48.0mm
	Nominal Diameter (Imperial)	1-1/4"
	Nominal Diameter (Metric)	42mm
	Thickness T (Imperial)	0.20"
	Thickness T (Metric)	5mm
Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1

166-50174



Logistic and
Packaging

Package Quantity (Metric)

1