

166-50175



Article Number: 166-50175

Description: HelaGuard Metal Locknuts, Metric Thread, 50mm, Nickel Plated Brass, Silver, 1/pkg

Base Data	Local Order Number	166-50175
	Type	ALNPB-M50
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> <li>• Nickel plated brass thread ensures secure connection with brass plated fittings.</li> <li>• Metric thread pattern works with metric thread fittings.</li> </ul>
	Quantity Per	bag
	Product Description	Locknuts work with metric threaded fittings or knockout entries.
	Short Description	HelaGuard Metal Locknuts, Metric Thread, 50mm, Nickel Plated Brass, Silver, 1/pkg
	Product Dimensions	Wrenching Flat Size (Imperial)
Wrenching Flat Size (Metric)		58.0mm
Nominal Diameter (Imperial)		2-1/8"
Nominal Diameter (Metric)		54mm
Thickness T (Imperial)		0.24"
Thickness T (Metric)		6mm
Material and Specifications		Material
	Material Shortcut	NPB
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	Logistic and Packaging	Package Quantity (Imperial)

166-50175

**HellermannTyton**

Logistic and  
Packaging

Package Quantity (Metric)

1