

166-90015

HellermannTyton

Article Number: 166-90015



Description: HelaGuard Non-Metallic IP68 Conduit Reducer, 1.25" down-to 0.50" Dia, PA66, Black, 5/pkg

Base Data		
	Local Order Number	166-90015
	Type	HGL050-R125
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Used to join conduits of different diameters. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • Vibration and shock tested to EN61373 Category 2. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	bag
	Product Description	Conduit Reducers are used with T-Connectors to combine different conduit diameters. Suitable for use on all types of corrugated conduits, both fine and coarse pitch material. Nylon material provides high resistance to oils and solvents, with great durability and extremely high extraction force. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP68 Conduit Reducer, 1.25" down-to 0.50" Dia, PA66, Black, 5/pkg
Product Dimensions		
	Length L (Imperial)	2.35"
	Length L (Metric)	59.8mm
	Bore Diameter (Imperial)	0.69"
	Bore Diameter (Metric)	17.5mm
	Euro (NW) Size	36mm
	Reduce to Euro (NW) Size	17
	Reduce to Trade Size	1/2 "
	Swivel Thread (Y/N)	No
	To Nominal Diameter (Imperial)	0.50"
	Trade Size	1-1/4 "
	Variant	Reducer

166-90015



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5Pieces