

166-90019

HellermannTyton



Article Number: 166-90019

Description: HelaGuard Non-Metallic Locknut, NPT Thread, 0.50" Dia, PA66, Black, 10/pkg

Base Data		
	Local Order Number	166-90019
	Type	ALPA0500
	Color	Black (BK)
	Features and benefits	• Ensures fast and secure assembly with non-metallic NPT fittings.
	Quantity Per	bag
	Product Description	Made of strong and chemical resistant PA66 material, locknut secures non-metallic NPT fittings when used with non-threaded entries.
	Short Description	HelaGuard Non-Metallic Locknut, NPT Thread, 0.50" Dia, PA66, Black, 10/pkg
Product Dimensions		
	Fits Conduit Size (Imperial)	1/2 "
	Fits Conduit Size (Metric)	21mm
	Wrenching Flat Size (Imperial)	1.06"
	Wrenching Flat Size (Metric)	26.9mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	21mm
	Thickness T (Imperial)	0.265"
	Thickness T (Metric)	6.7mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes

166-90019



Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	3926909987