

166-90087

HellermannTyton

Article Number: 166-90087



Description: HelaGuard Non-Metallic IP66 Fitting, 45-Elbow Brass Swivel, Int. Metric Thread, 1.50" (50mm) Dia, PA66 NPB, Bk, 2/pkg

Base Data	
Local Order Number	166-90087
Type	HG150-45F-M50
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Internal nickel-plated brass metric thread provides a secure connection. • Swivel feature minimizes cable twisting, providing strain relief. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • Elbow features a smooth, swept bore to ease cable installation. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
Product Description	Elbow fitting features a snap-on design and a nickel-plated brass metric thread that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
Short Description	HelaGuard Non-Metallic IP66 Fitting, 45-Elbow Brass Swivel, Int. Metric Thread, 1.50" (50mm) Dia, PA66 NPB, Bk, 2/pkg
Product Dimensions	
Length L (Imperial)	2.15"
Length L (Metric)	54.5mm
Bore Diameter (Imperial)	1.51"
Bore Diameter (Metric)	39.0mm
Clearance Hole Diameter (Imperial)	2.469"
Clearance Hole Diameter (Metric)	62.71mm
Thread Length (Imperial)	0.55"
Outside Diameter D (imperial)	2.99"
Outside Diameter OD (metric)	76mm
Nominal Diameter (Imperial)	2-1/8"
Nominal Diameter (Metric)	54mm

166-90087



Product Dimensions	Thread Length (metric)	14mm
Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces