

166-90110

HellermannTyton

Article Number: 166-90110



Description: HelaGuard Non-Metallic IP68 Fitting, 45-Elbow, NPT Thread, 0.75" Dia, Black, 10/pkg

Base Data		
	Local Order Number	166-90110
	Type	HGL075-45-0750
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • Elbow features a smooth, swept bore to ease cable installation. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	bag
	Product Description	Elbow fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP68 Fitting, 45-Elbow, NPT Thread, 0.75" Dia, Black, 10/pkg
Product Dimensions		
	Length L (Imperial)	2.87"
	Length L (Metric)	73mm
	Bore Diameter (Imperial)	0.75"
	Bore Diameter (Metric)	19.0mm
	Clearance Hole Diameter (Imperial)	1.039"
	Clearance Hole Diameter (Metric)	26.4mm
	Euro (NW) Size	23mm
	Swivel Thread (Y/N)	No
	Thread Length (Imperial)	0.59"
	Thread Type	NPT
	Trade Size	3/4 "

166-90110



Product Dimensions	Variant	45° Elbow
	Outside Diameter D (imperial)	1.73"
	Outside Diameter OD (metric)	44mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	28mm
	Thread Length (metric)	15mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
	UL Listed (US)	Yes
	UL Recognized (US)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	3926909987