

166-90123

# HellermannTyton

Article Number: 166-90123



Description: HelaGuard Non-Metallic Fitting, IP68, Straight, 1.5" NPT Thread, 1.50" Dia, PA66, Black, 2/pkg

Base Data		
	Local Order Number	166-90123
	Type	HGL150-S-1500
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• External NPT thread provides a secure connection.</li> <li>• Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.</li> <li>• All-around "teeth" attach firmly to conduit and deliver a high extraction force.</li> <li>• Durable nylon material has high resistance to salts, oils, weak acids and solvents.</li> <li>• IP66 fitting has one-piece construction.</li> <li>• IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.</li> </ul>
	Quantity Per	bag
	Product Description	Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic Fitting, IP68, Straight, 1.5" NPT Thread, 1.50" Dia, PA66, Black, 2/pkg
Product Dimensions		
	Length L (Imperial)	2.64"
	Length L (Metric)	67.0mm
	Bore Diameter (Imperial)	1.65"
	Bore Diameter (Metric)	42.0mm
	Clearance Hole Diameter (Imperial)	1.882"
	Clearance Hole Diameter (Metric)	47.8mm
	Euro (NW) Size	48mm
	Swivel Thread (Y/N)	No
	Thread Length (Imperial)	0.71"
	Thread Type	NPT
	Trade Size	1-1/2 "
	Variant	Straight

166-90123



Product Dimensions	Outside Diameter D (imperial)	2.99"
	Outside Diameter OD (metric)	76.0mm
	Nominal Diameter (Imperial)	2-1/8"
	Nominal Diameter (Metric)	54mm
	Thread Length (metric)	18mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	UL Listed (US)	Yes
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces
	Customs Number(Schedule B)	3926909987