

166-90133

HellermannTyton

Article Number: 166-90133



Description: HelaGuard Non-Metallic IP65 Fitting, Straight, NPT Thread, 0.38" Dia, PA66, Black, 10/pkg

| | | |
|--------------------|------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base Data | | |
| | Local Order Number | 166-90133 |
| | Type | PSR038-S-0380 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Twist-on installation makes future access fast and easy. • Internal spigot design helps ease threading of fitting onto conduit. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP65 rating for protection against wind, dirt and low pressure jets of water from all directions. |
| | Quantity Per | bag |
| | Product Description | Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing. |
| | Short Description | HelaGuard Non-Metallic IP65 Fitting, Straight, NPT Thread, 0.38" Dia, PA66, Black, 10/pkg |
| Product Dimensions | | |
| | Length L (Imperial) | 1.57" |
| | Length L (Metric) | 40mm |
| | Bore Diameter (Imperial) | 0.41" |
| | Bore Diameter (Metric) | 10.5mm |
| | Clearance Hole Diameter (Imperial) | 0.657" |
| | Clearance Hole Diameter (Metric) | 16.7mm |
| | Thread Length (Imperial) | 0.43" |
| | Trade Size | 3/8 " |
| | Outside Diameter D (imperial) | 1.10" |
| | Outside Diameter OD (metric) | 28mm |
| | Nominal Diameter (Imperial) | 3/8" |
| | Nominal Diameter (Metric) | 16mm |
| | Thread Length (metric) | 11mm |

166-90133



| | | |
|-----------------------------|-------------------------------|-----------------------------------|
| Material and Specifications | | |
| | Material | Polyamide 6.6 (PA66) |
| | Material Shortcut | PA66 |
| | Flammability | UL 94 V2 |
| | Operating Temperature | -40°F to +248°F (-40°C to +120°C) |
| | ROHS Compliant | Yes |
| | UL Recognized (US and Canada) | Yes |
| | UL Recognized (US) | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 10 |
| | Package Quantity (Metric) | 10Pieces |
| | Customs Number(Schedule B) | 3926909987 |