

166-90154

# HellermannTyton

Article Number: 166-90154



Description: HelaGuard Non-Metallic IP68 Fitting, 45-Flange, Swivel, 0.50" Dia, PA66, Black, 10/pkg

Base Data		
	Local Order Number	166-90154
	Type	HGL050-45FL
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Flange provides easy installation to flat surfaces.</li> <li>• Swivel feature minimizes cable twisting, providing strain relief.</li> <li>• Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.</li> <li>• Elbow features a smooth, swept bore to ease cable installation.</li> <li>• All-around "teeth" attach firmly to conduit and deliver a high extraction force.</li> <li>• Durable nylon material has high resistance to salts, oils, weak acids and solvents.</li> <li>• IP66 fitting has one-piece construction.</li> <li>• IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.</li> </ul>
	Quantity Per	bag
	Product Description	Elbow fitting with flange features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP68 Fitting, 45-Flange, Swivel, 0.50" Dia, PA66, Black, 10/pkg
Product Dimensions		
	Length L (Imperial)	2.48"
	Length L (Metric)	63mm
	Bore Diameter (Imperial)	0.55"
	Bore Diameter (Metric)	14.0mm
	Euro (NW) Size	17mm
	Swivel Thread (Y/N)	No
	Trade Size	1/2 "
	Variant	45° Elbow Flange
	Outside Diameter D (imperial)	1.34"
	Outside Diameter OD (metric)	34mm
	Nominal Diameter (Imperial)	1/2"

166-90154

**HellermannTyton**

Product Dimensions	Nominal Diameter (Metric)	21mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces