

166-90166

HellermannTyton

Article Number: 166-90166



Description: HelaGuard Non-Metallic IP68 Fitting, Straight Swivel Flange, 1.00" Dia, PA66, Black, 10/pkg

Base Data		
	Local Order Number	166-90166
	Type	HGL100-SFL
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Flange provides easy installation to flat surfaces. • Swivel feature minimizes cable twisting, providing strain relief. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	bag
	Product Description	Straight flange fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP68 Fitting, Straight Swivel Flange, 1.00" Dia, PA66, Black, 10/pkg
Product Dimensions		
	Length L (Imperial)	2.17"
	Length L (Metric)	55mm
	Bore Diameter (Imperial)	1.04"
	Bore Diameter (Metric)	26.5mm
	Euro (NW) Size	29mm
	Swivel Thread (Y/N)	No
	Trade Size	1 "
	Variant	Straight Flange
	Outside Diameter D (imperial)	2.01"
	Outside Diameter OD (metric)	51mm
	Nominal Diameter (Imperial)	1"

166-90166

HellermannTyton

Product Dimensions	Nominal Diameter (Metric)	34mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces