

166-90172

HellermannTyton

Article Number: 166-90172



Description: HelaGuard Non-Metallic IP68 Fitting, T-Connector, 1.25" Dia, PA66, Black, 2/pkg

Base Data		
	Local Order Number	166-90172
	Type	HGL125-T
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Used to join conduits of same diameters and route to multiple directions. • Inspection lid facilitates cable pull through and eases installation. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • Vibration and shock tested to EN61373 Category 2. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	bag
	Product Description	T- Connectors are used to join three same diameter corrugated conduits together, and redirect cables into multiple directions. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP68 Fitting, T-Connector, 1.25" Dia, PA66, Black, 2/pkg
Product Dimensions		
	Length L (Imperial)	4.33"
	Length L (Metric)	110mm
	Bore Diameter (Imperial)	1.61"
	Bore Diameter (Metric)	41.0mm
	Euro (NW) Size	36mm
	Swivel Thread (Y/N)	No
	Trade Size	1-1/4 "
	Variant	T-Connector
	Outside Diameter D (imperial)	5.91"
	Outside Diameter OD (metric)	150mm

166-90172

HellermannTyton

Product Dimensions	Nominal Diameter (Imperial)	1-1/4"
	Nominal Diameter (Metric)	42mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces