

166-90176

HellermannTyton



Article Number: 166-90176

Description: HelaGuard Non-Metallic IP66 Fitting, T-Connector, 1.00" Dia, PA66, Black, 2/pkg

Base Data

Local Order Number	166-90176
Type	HG100-T
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Used to join conduits of same diameters and route to multiple directions. • Inspection lid facilitates cable pull through and eases installation. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • Vibration and shock tested to EN61373 Category 2. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
Quantity Per	bag
Product Description	T- Connectors are used to join three same diameter corrugated conduits together, and redirect cables into multiple directions. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
Short Description	HelaGuard Non-Metallic IP66 Fitting, T-Connector, 1.00" Dia, PA66, Black, 2/pkg

Product Dimensions

Length L (Imperial)	3.58"
Length L (Metric)	91mm
Bore Diameter (Imperial)	1.30"
Bore Diameter (Metric)	33.0mm
Euro (NW) Size	29mm
Swivel Thread (Y/N)	No
Trade Size	1 "
Variant	T-Connector
Outside Diameter D (imperial)	5.12"
Outside Diameter OD (metric)	130mm

166-90176

HellermannTyton

Product Dimensions	Nominal Diameter (Imperial)	1"
	Nominal Diameter (Metric)	34mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces
	Customs Number(Schedule B)	3926909987