

166-90195

HellermannTyton



Article Number: 166-90195

Description: HelaGuard Non-Metallic Conduit, Std. Weight, 1.50" Dia, Nylon PA6, Black, 50 ft/std reel

Base Data		
	Local Order Number	166-90195
	Type	HG-SW1500
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Material is easy to use and cut; reduces installation time and labor costs. • Flexible, abrasion resistant and durable for a variety of applications. • Good impact strength; recovers quickly if crushed. • UV resistant; suitable for use in outdoor applications. • Offered in fine or coarse corrugated pitch.
	Quantity Per	reel
	Product Description	A standard weight corrugated conduit made of PA6 nylon that offers flexible abrasion protection for wire and cable bundles. Easy to cut and use, the material is highly resistant to solvents and oils. Combine with HelaGuard non-metallic fittings for IP66 rating or greater protection against water, wind and dirt.
	Short Description	HelaGuard Non-Metallic Conduit, Std. Weight, 1.50" Dia, Nylon PA6, Black, 50 ft/std reel
Product Dimensions		
	Length L (Imperial)	50.0ft
	Length L (Metric)	15.2m
	Inner Diameter D (Imperial)	1.86"
	Inner Diameter ID (metric)	47.2mm
	Euro (NW) Size	48mm
	Pitch Type	C (Coarse)
	Trade Size	1-1/2 "
	Outside Diameter D (imperial)	2.15"
	Outside Diameter OD (metric)	54.5mm
	Nominal Diameter (Imperial)	1-1/2"
	Nominal Diameter (Metric)	54mm
	Inside Bend Radius (Imperial)	3.15"
	Inside Bend Radius (Metric)	80mm

166-90195



Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	PA6
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
	UL Listed (US)	Yes
	UL Listed (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50ft
	Package Quantity (Metric)	15.2m
	Customs Number(Schedule B)	3926909987