

166-90234

HellermannTyton

Article Number: 166-90234



Description: HelaGuard Non-Metallic Fitting, Conduit Coupler, IP66, 1.50" to 1.50" Dia, PA66, Black, 2/pkg

Base Data		
	Local Order Number	166-90234
	Type	HG150-HG150
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • One-piece fitting used to join conduits of same diameters. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 ingress protection rating against water, dust and wind.
	Quantity Per	bag
	Product Description	Used to join two same diameter corrugated conduits together, couplers feature a snap-on design for a quick, secure connection. Designed for easy removal with a small screwdriver. Suitable for use on all types of corrugated conduits, both fine and course pitch material.
	Short Description	HelaGuard Non-Metallic Fitting, Conduit Coupler, IP66, 1.50" to 1.50" Dia, PA66, Black, 2/pkg
Product Dimensions		
	Length L (Imperial)	4.49"
	Length L (Metric)	114mm
	Bore Diameter (Imperial)	1.65"
	Bore Diameter (Metric)	42.0mm
	Swivel Thread (Y/N)	No
	To Nominal Diameter (Imperial)	1-1/2
	Variant	Coupler
	Outside Diameter D (imperial)	2.99"
	Outside Diameter OD (metric)	76mm
	Nominal Diameter (Imperial)	2-1/8"
	Nominal Diameter (Metric)	54mm

166-90234



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces