

166-90239



Article Number: 166-90239

Description: HelaGuard REC Conduit End Cap, 1.25" Dia, Flexible Rubber, Black, 10/pkg

Base Data		
	Local Order Number	166-90239
	Type	REC1250
	Color	Black (BK)
	Features and benefits	• Flexible rubber material easily slips over end of conduit to seal out dust and debris. • Diameter markings make it easy to cut down to appropriate size. • Contains a cable tie slot for extra retention when required.
	Quantity Per	pack
	Product Description	Rubber cap easily slides over un-terminated conduit and tubing ends to protect inside wire and cable bundles from debris. For use with HelaGuard conduits and tubing.
	Short Description	HelaGuard REC Conduit End Cap, 1.25" Dia, Flexible Rubber, Black, 10/pkg
Product Dimensions		
	Length L (Imperial)	1.85"
	Length L (Metric)	47mm
	Fits Conduit Size (Imperial)	1-1/4 "
	Fits Conduit Size (Metric)	42mm
	Outside Diameter D (imperial)	2.02"
	Outside Diameter OD (metric)	51.3mm
	Nominal Diameter (Imperial)	1-1/4"
	Nominal Diameter (Metric)	42mm
Material and Specifications		
	Material	Rubber
	Material Shortcut	CR
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-58°F to +248°F (-50°C to +120°C)

166-90239



Material and Specifications	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	3926909987