

166-90307

# HellermannTyton

Article Number: 166-90307



Description: HelaGuard Non-Metallic IP66 Fitting, Straight, 2" NPT Thread, 1.5" Dia., PA66, Black, 1/pkg

Base Data		
	Local Order Number	166-90307
	Type	HG150-S-2000
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• External NPT thread provides a secure connection.</li> <li>• Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.</li> <li>• All-around "teeth" attach firmly to conduit and deliver a high extraction force.</li> <li>• Durable nylon material has high resistance to salts, oils, weak acids and solvents.</li> <li>• IP66 fitting has one-piece construction.</li> <li>• IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.</li> </ul>
	Quantity Per	bag
	Product Description	Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, 2" NPT Thread, 1.5" Dia., PA66, Black, 1/pkg
Product Dimensions		
	Length L (Imperial)	2.72"
	Length L (Metric)	69mm
	Outside Diameter D (imperial)	2.99"
	Outside Diameter OD (metric)	76mm
	Nominal Diameter (Imperial)	2-1/8"
	Nominal Diameter (Metric)	54mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2

166-90307



Material and Specifications	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	1Pieces