

166-90362

HellermannTyton

Article Number: 166-90362



Description: LPC Metallic IP68 Compression Fitting, Straight Brass Swivel, Ext. 1/2" NPT Thread, 0.50" (20mm) Dia, NPB Metal, 10/pkg

Base Data		
	Local Order Number	166-90362
	Type	LPC050-S-050
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> • External nickel-plated brass NPT thread provides a durable connection. • Swivel feature allows fitting to rotate until tightened. • Metal ferrule insert has shallow & longer scroll for stronger fit with LPC smooth bore PVC tubings. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	pack
	Product Description	Multi-part metallic straight compression style fitting for use with LPC non metallic PVC tubing. Suitable for NPT threaded entries or knocknuts as fitting rotates until tightened. A longer and shallower scroll allows quick assembly and more durable fit with smooth bore tubing. Provides IP68 and up to IP69 ingress protection.
	Short Description	LPC Metallic IP68 Compression Fitting, Straight Brass Swivel, Ext. 1/2" NPT Thread, 0.50" (20mm) Dia, NPB Metal, 10/pkg
Product Dimensions		
	Length L (Imperial)	1.32"
	Length L (Metric)	33.5mm
	Length L2 (Imperial)	0.85"
	Bore Diameter (Imperial)	0.57"
	Bore Diameter (Metric)	14.5mm
	Length L2 (Metric)	21.5mm
	Thread Length (Imperial)	0.47"
	Thread Size (Imperial)	1/2 "
	Height H (Imperial)	1.14"
	Height H (Metric)	29.0mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	20mm
	Thread Length (metric)	12.0mm

166-90362



Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	8547900030