

166-90367

HellermannTyton

Article Number: 166-90367



Description: HelaGuard Non-Metallic IP66 Fitting, Y-Divider, 1/2" reduce to 3/8", 0.50" Dia, PA66, Black, 3/pkg

Base Data		
	Local Order Number	166-90367
	Type	HG050-Y038
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Conduit divider fitting used to reduce conduit run diameter sizes. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water.
	Quantity Per	bag
	Product Description	Y-Divider connectors are used to reduce diameter of conduit runs and re-direct in side-by-side direction. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings.
	Short Description	HelaGuard Non-Metallic IP66 Fitting, Y-Divider, 1/2" reduce to 3/8", 0.50" Dia, PA66, Black, 3/pkg
Product Dimensions		
	To Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	16mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)

166-90367



Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	3Pieces