

166-90383

HellermannTyton

Article Number: 166-90383

 Description: Liquid-Tight Metallic Conduit, Flexible, 1.0" (32mm) Dia,
Galvanized Steel w/PVC Cover, Black, 82ft/Reel


Base Data		
	Local Order Number	LTP32B-25M
	Type	LTS1000-25M
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL series fittings. • Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance. • Smooth PVC cover resists oil and grease and will not wrinkle when conduit is bent; also resistant to acids. • UV-resistant (black), suitable for outdoor use. • Manufactured to UL360 requirements.
	Quantity Per	reel
	Product Description	A flexible, liquid-tight galvanized steel conduit with a smooth oil resistant PVC coating. LTP series is a general purpose, non-UL rated liquid-tight conduit used in applications that require movement, vibration and bending. Use with LTP or LTPUL series metallic fittings for IP66 + IP67 + IP68 + IP69 ratings. Designed for applications where a UL listing or CSA certification is not required but where a need still exists for a flexible metal conduit to protect wires against impact and exposure to oils and chemicals. May be used in hazardous locations when accompanied with LTPUL or EXD metallic fittings.
	Technical Description	Manufacturer Reference Number: LTP32B-25M
Product Dimensions	Short Description	Liquid-Tight Metallic Conduit, Flexible, 1.0" (32mm) Dia, Galvanized Steel w/PVC Cover, Black, 82ft/Reel
	Length L (Imperial)	82.0ft
	Length L (Metric)	25.0m
	Reel Length (imperial)	82.0ft
	Diameter D (imperial)	1.04"
	Diameter D (metric)	26.5mm
	Outside Diameter D (imperial)	1.30"
	Outside Diameter OD (metric)	33.1mm
	Nominal Diameter (Imperial)	1"
	Nominal Diameter (Metric)	32.0mm

166-90383



Product Dimensions	Inside Bend Radius (Metric)	135mm
Material and Specifications		
	Material	Galvanised Steel (GS)
	Material Shortcut	PVC
	Flammability	Self-Extinguishing according to EN IEC 61386-1
	Operating Temperature	-4°F to +221°F (-20°C to +105°C)
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25.0m
	Weight (Metric)	18.3kg
	Weight (imperial)	40.3lbs