

166-90418

HellermannTyton

Article Number: 166-90418



Description: Liquid-Tight Metallic Comp Fitting, Flexible, Coupler, 0.50" (20mm) to 0.50" (20mm) Dia, NPB Metal, 2/pkg

Base Data		
	Local Order Number	LTP20-LTP20
	Type	LTS050-LTS050
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> • Low profile design eases access and installation in tight-fit applications. • Multipart compression fitting includes polyamide seal for sealing out moisture to obtain IP66, IP67, IP68 and IP69 ingress protection levels. • Durable nickel plated brass material provides high mechanical and tensile strength and resistance to oil & corrosion. • Interchangeable with all liquid-tight metallic conduits made to UL360 sizes.
	Quantity Per	pack
	Product Description	Multi-part nickel plated brass compression coupler for joining two liquid-tight metallic conduits. Coupler consists of a threaded body, two wrenching nuts, grounding ferrule and nylon compression seal.
	Technical Description	Manufacturer Reference Number: LTP20-LTP20
	Short Description	Liquid-Tight Metallic Comp Fitting, Flexible, Coupler, 0.50" (20mm) to 0.50" (20mm) Dia, NPB Metal, 2/pkg
Product Dimensions		
	Length L (Imperial)	39.5"
	Length L (Metric)	39.5mm
	Bore Diameter (Imperial)	0.57"
	Bore Diameter (Metric)	14.5mm
	Wrenching Flat Size (Imperial)	1.56"
	Wrenching Flat Size (Metric)	39.5mm
	Height H (Imperial)	1.14"
	Height H (Metric)	29.0mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	20.0mm

166-90418



Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces