

166-90465

# HellermannTyton



Article Number: 166-90465

Description: HelaGuard Non-Metallic Conduit, Light Weight, 2.0" Dia, Nylon PA6, Black, 25ft/Std. Reel

Base Data		
	Local Order Number	166-90465
	Type	HG-LW2000
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Lightweight and highly flexible for use in tight bend and fit applications.</li> <li>• Easy to use and cut; reduces installation time and labor costs.</li> <li>• Good abrasion resistance and impact strength; recovers quickly if crushed.</li> <li>• Offered in fine or course corrugated pitch.</li> </ul>
	Quantity Per	reel
	Product Description	Lightweight nylon corrugated conduit provides high flexibility and good mechanical protection of wire and cable bundles, especially useful in smaller bend radius tight-fit applications. PA6 material offers high resistance to oils and solvents, along with good abrasion protection. Combine with HelaGuard non-metallic fittings for IP66 rating or greater protection against water, wind and dirt.
	Short Description	HelaGuard Non-Metallic Conduit, Light Weight, 2.0" Dia, Nylon PA6, Black, 25ft/Std. Reel
Product Dimensions		
	Length L (Imperial)	25.0ft
	Length L (Metric)	7.6m
	Outside Diameter D (imperial)	2.65"
	Outside Diameter OD (metric)	67.2mm
	Nominal Diameter (Imperial)	2-5/8"
	Nominal Diameter (Metric)	67mm
Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	PA6
	Flammability	Self-Extinguishing according to EN IEC 61386
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)

166-90465



Logistic and Packaging		
	Package Quantity (Imperial)	25ft
	Package Quantity (Metric)	7.6m
	Customs Number(Schedule B)	3926909987