

166-90480

HellermannTyton

Article Number: 166-90480

Description: HelaGuard 3/8" Rubber Sealing Washer, Chloroprene Rubber, Black, 10 pcs/pkg

| | | |
|-----------------------------|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base Data | | |
| | Local Order Number | 166-90480 |
| | Type | SW0380 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none">• Protects against water and dust.• 80 Shore A compression strength.• For NPT threads.• Resistant to oil. |
| | Quantity Per | pack |
| | Product Description | Chloroprene rubber sealing washer for use with non-metallic threaded fittings. |
| | Short Description | HelaGuard 3/8" Rubber Sealing Washer, Chloroprene Rubber, Black, 10 pcs/pkg |
| Product Dimensions | | |
| | Outside Diameter D (imperial) | 0.95" |
| | Outside Diameter OD (metric) | 24mm |
| | Nominal Diameter (Imperial) | 3/8" |
| | Nominal Diameter (Metric) | 16mm |
| Material and Specifications | | |
| | Material | Chloroprene (CR) |
| | Material Shortcut | CR |
| | Operating Temperature | -40°F to +275°F (-40°C to +135°C) |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 10 |
| | Package Quantity (Metric) | 10Pieces |

