

166-90505

# HellermannTyton

Article Number: 166-90505



Description: HelaGuard Non-Metallic IP65 Compression Fitting,  
Straight, NPT Thread, 1.50" Dia, Black, 1/pkg

Base Data		
	Local Order Number	166-90505
	Type	PSR150-S-1500
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• External NPT thread provides a secure connection.</li> <li>• Twist-on installation makes future access fast and easy.</li> <li>• Internal spigot design helps ease threading of fitting onto conduit.</li> <li>• All-around "teeth" attach firmly to conduit and deliver a high extraction force.</li> <li>• Durable nylon material has high resistance to salts, oils, weak acids and solvents.</li> <li>• IP65 rating for protection against wind, dirt and low pressure jets of water from all directions.</li> </ul>
	Quantity Per	pack
	Product Description	Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing.
	Short Description	HelaGuard Non-Metallic IP65 Compression Fitting, Straight, NPT Thread, 1.50" Dia, Black, 1/pkg
Product Dimensions		
	Length L (Imperial)	2.17"
	Length L (Metric)	55.0mm
	Clearance Hole Diameter (Imperial)	1.54"
	Clearance Hole Diameter (Metric)	1.89mm
	Thread Length (Imperial)	0.63"
	Trade Size	1-1/2 "
	Outside Diameter D (imperial)	2.52"
	Outside Diameter OD (metric)	64.0mm
	Nominal Diameter (Imperial)	2"
	Nominal Diameter (Metric)	50mm
	Thread Length (metric)	16.0mm

166-90505



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1258
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	3926909987