

166-90507

# HellermannTyton

Article Number: 166-90507



Description: Metallic Compression Fitting, Straight Swivel, M16 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg

Base Data		
	Local Order Number	FSU16-M16-C-S
	Type	FSU16-M16-C-S
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> <li>• Nickel plated brass compression fitting used with FSU, LFHU and FPU flexible metallic conduit.</li> <li>• Two part swivel fitting comprised of shell, body and elastomer seal delivers IP65 ingress protection.</li> <li>• External thread swivels about main body even after tightening.</li> </ul>
	Quantity Per	pack
	Product Description	Two-part nickel plated brass straight fitting with swivel external metric thread. Fitting comprised of shell and body suitable for knockout or threaded metric entries. For use with FSU, FPU, and LFHU flexible metal conduit.
	Technical Description	Manufacturer Reference Number: FSU16-M16-C-S
	Short Description	Metallic Compression Fitting, Straight Swivel, M16 Metric Thread, 3/8" (16mm) Dia, NPB Metal, 10/pkg
Product Dimensions		
	Length L (Imperial)	1.61"
	Length L (Metric)	40.9mm
	Bore Diameter (Imperial)	0.45"
	Bore Diameter (Metric)	11.5mm
	Thread Length (Imperial)	0.39"
	Wrenching Flat Size (Imperial)	1.22"
	Wrenching Flat Size (Metric)	30.9mm
	Height H (Imperial)	1.02"
	Height H (Metric)	26.0mm
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	16.0mm
	Thread Length (metric)	10mm
	Thread Size (Metric)	M16

166-90507



Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces