

166-90535

HellermannTyton

Article Number: 166-90535



Description: Metallic Compression Fitting, Straight, 1/2" NPT Thread, 0.5" (20mm) Dia, NPB Metal, 10/pkg

Base Data		
	Local Order Number	FSU20-050-C
	Type	FSU20-050-C
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> • Nickel plated brass compression fitting used with FSU, LFHU and FPU flexible metallic conduit. • Fitting includes elastomeric sealing washer for IP65 ingress protection. • Suitable for knockouts or NPT / Metric threaded entries as fitting rotates until tightened.
	Quantity Per	pack
	Product Description	Multipart straight compression fitting with fixed external thread pattern suitable for threaded or knockout entries. Constructed with nickel plated brass components that resist corrosion, ensures high mechanical strength and electrical continuity. Fitting comprised of body, nut, grounding ferrule and nylon compression seal. For use with FSU, FPU, and LFHU flexible metal conduits.
	Technical Description	Manufacturer Reference Number: FSU20-050-C
	Short Description	Metallic Compression Fitting, Straight, 1/2" NPT Thread, 0.5" (20mm) Dia, NPB Metal, 10/pkg
Product Dimensions		
	Length L (Imperial)	1.36"
	Length L (Metric)	34.5mm
	Bore Diameter (Imperial)	0.57"
	Bore Diameter (Metric)	14.5mm
	Thread Length (Imperial)	0.51"
	Wrenching Flat Size (Imperial)	0.85"
	Wrenching Flat Size (Metric)	21.5mm
	Height H (Imperial)	0.85"
	Height H (Metric)	26.0mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	20.0mm

166-90535



Product Dimensions	Thread Length (metric)	13mm
Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	PA6
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces