

166-90551

HellermannTyton

Article Number: 166-90551



Description: Metallic Compression Fitting, Fixed Straight, M32 Metric Thread, 1" (32mm) Dia, NPB Metal, 2/pkg

Base Data		
	Local Order Number	FSU32-M32-M
	Type	FSU32-M32-M
	Color	Metal (ML)
	Features and benefits	• Nickel plated brass compression fitting used with FSU, LFHU and FPU flexible metallic conduit. • Two part fitting comprised of shell and body with external metric thread delivers IP54 ingress protection. • Suitable for knockouts and secured with a metric threaded locknut.
	Quantity Per	pack
	Product Description	Two-part nickel plated brass straight fitting with fixed external metric thread. Fitting comprised of shell and body suitable for knockout entries. For use with FSU, FPU and LFHU flexible metal conduit.
	Technical Description	Manufacturer Reference Number: FSU32-M32-M
	Short Description	Metallic Compression Fitting, Fixed Straight, M32 Metric Thread, 1" (32mm) Dia, NPB Metal, 2/pkg
Product Dimensions		
	Length L (Imperial)	1.45"
	Length L (Metric)	36.8mm
	Bore Diameter (Imperial)	1.03"
	Bore Diameter (Metric)	26.2mm
	Thread Length (Imperial)	0.51"
	Wrenching Flat Size (Imperial)	1.45"
	Wrenching Flat Size (Metric)	36.8mm
	Height H (Imperial)	1.42"
	Height H (Metric)	36.0mm
	Nominal Diameter (Imperial)	1"
	Nominal Diameter (Metric)	32.0mm
	Thread Length (metric)	13mm
	Thread Size (Metric)	M32

166-90551



Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +572°F (-50°C to +300°C)
Logistic and Packaging		
	Package Quantity (Imperial)	2
	Package Quantity (Metric)	2Pieces