

166-90633

HellermannTyton



Article Number: 166-90633

Description: Hazardous Area Metallic Thread Converter, M25
External/M32 Internal Thread, NPB Metal, 1/pkg

Base Data		
	Local Order Number	B-M25-M32-EXD
	Type	B-M25-M32-EXD
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> • Quickly converts thread size or style for use in threaded entries. • Obtain IP68 level ingress protection with use of sealing washer. • Suitable for use in Zone 1, Zone 2, Zone 21 and Zone 22 hazardous areas. • ATEX and IECEx EX d (Flameproof). • ATEX and IECEx EX e (Increased Safety). • ATEX and IECEx EX t (Dust Ignition Protection).
	Quantity Per	pack
	Product Description	Nickel plated brass thread converters used to increase, reduce or convert thread types in hazardous environments. For use with Flexicon's LTP-EXD fittings. Achieves IP68 level ingress protection with use of sealing washer.
	Technical Description	Manufacturer Reference Number: B-M25-M32-EXD
	Short Description	Hazardous Area Metallic Thread Converter, M25 External/M32 Internal Thread, NPB Metal, 1/pkg
Product Dimensions		
	External Thread Size (metric)	M25
	Height H (Imperial)	1.53"
	Height H (Metric)	38.9mm
Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1

