

166-90640

# HellermannTyton



Article Number: 166-90640

Description: Hazardous Area Metallic Thread Converter, 1/2" NPT External/M20 Internal Thread, NPB Metal, 1/pkg

Base Data		
	Local Order Number	B-050-M20--EXD
	Type	B-050-M20-EXD
	Color	Metal (ML)
	Features and benefits	<ul style="list-style-type: none"> <li>• Quickly converts thread size or style for use in threaded entries.</li> <li>• Obtain IP68 level ingress protection with use of sealing washer.</li> <li>• Suitable for use in Zone 1, Zone 2, Zone 21 and Zone 22 hazardous areas.</li> <li>• ATEX and IECEx EX d (Flameproof).</li> <li>• ATEX and IECEx EX e (Increased Safety).</li> <li>• ATEX and IECEx EX t (Dust Ignition Protection).</li> </ul>
	Quantity Per	pack
	Product Description	Nickel plated brass thread converters used to increase, reduce or convert thread types in hazardous environments. For use with Flexicon's LTP-EXD fittings. Achieves IP68 level ingress protection with use of sealing washer.
	Technical Description	Manufacturer Reference Number: B-050-M20--EXD
	Short Description	Hazardous Area Metallic Thread Converter, 1/2" NPT External/M20 Internal Thread, NPB Metal, 1/pkg
Product Dimensions		
	Height H (Imperial)	1.02"
	Height H (Metric)	25.9mm
Material and Specifications		
	Material	Nickel Plated Brass (NPB)
	Material Shortcut	NPB
	Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1

