

166-90642

HellermannTyton



Article Number: 166-90642

Description: Hazardous Area Metallic Thread Converter, 3/4" NPT
External/M25 Internal Thread, NPB Metal, 1/pkg

| | | |
|-----------------------------|-----------------------------|---|
| Base Data | | |
| | Local Order Number | B-075-M25--EXD |
| | Type | B-075-M25-EXD |
| | Color | Metal (ML) |
| | Features and benefits | <ul style="list-style-type: none"> • Quickly converts thread size or style for use in threaded entries. • Obtain IP68 level ingress protection with use of sealing washer. • Suitable for use in Zone 1, Zone 2, Zone 21 and Zone 22 hazardous areas. • ATEX and IECEx EX d (Flameproof). • ATEX and IECEx EX e (Increased Safety). • ATEX and IECEx EX t (Dust Ignition Protection). |
| | Quantity Per | pack |
| | Product Description | Nickel plated brass thread converters used to increase, reduce or convert thread types in hazardous environments. For use with Flexicon's LTP-EXD fittings. Achieves IP68 level ingress protection with use of sealing washer. |
| | Technical Description | Manufacturer Reference Number: B-075-M25--EXD |
| | Short Description | Hazardous Area Metallic Thread Converter, 3/4" NPT External/M25 Internal Thread, NPB Metal, 1/pkg |
| Product Dimensions | | |
| | Height H (Imperial) | 1.28" |
| | Height H (Metric) | 32.4mm |
| Material and Specifications | | |
| | Material | Nickel Plated Brass (NPB) |
| | Material Shortcut | NPB |
| | Operating Temperature | -58°F to +275°F (-50°C to +135°C) |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 1 |
| | Package Quantity (Metric) | 1 |

