

166-90659

# HellermannTyton

Article Number: 166-90659



Description: Liquid-Tight Metallic Conduit, Flexible, 0.38" (16mm) Dia, Galvanized Steel w/PVC Cover, Black, 82ft/Reel

Base Data		
	Local Order Number	LFHU16B-25M
	Type	LFHU16B-25M
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Highly durable spiral metallic conduit provides extra flexibility and delivers a high degree of compression strength and impact resistance.</li> <li>• Smooth low fire hazard cover resists oil and grease and will not crack under repeated bending.</li> <li>• Provides ingress protection performance to IP65 when used with FSU-styled fittings.</li> <li>• Tight bend radius for use in installations requiring constant movement or vibration.</li> <li>• Halogen Free.</li> </ul>
	Quantity Per	reel
	Product Description	An extra-flexible, galvanized steel conduit with a smooth oil resistant & low fire hazard coating. LFHU series is a spiral constructed, non-UL rated metallic conduit used in applications that demand higher levels of movement, bending and impact protection. Designed for applications within enclosed areas where limited smoke, low flame spread and low toxic gas emissions are required. Use with HelaGuard FSU Metallic Fittings for IP65 ratings.
	Technical Description	Manufacturer Reference Number: LFHU16B-25M
	Short Description	Liquid-Tight Metallic Conduit, Flexible, 0.38" (16mm) Dia, Galvanized Steel w/PVC Cover, Black, 82ft/Reel
Product Dimensions		
	Length L (Imperial)	82.0ft
	Length L (Metric)	25.0m
	Reel Length (imperial)	82.0ft
	Diameter D (imperial)	0.51"
	Diameter D (metric)	12.9mm
	Outside Diameter D (imperial)	0.67"
	Outside Diameter OD (metric)	17.1mm
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	16.0mm

166-90659

**HellermannTyton**

Product Dimensions	Inside Bend Radius (Imperial)	1.57"
	Inside Bend Radius (Metric)	40mm
Material and Specifications		
	Material	Galvanised Steel (GS)
	Material Shortcut	GS
	Flammability	Self-Extinguishing according to EN IEC 61386-1
	Operating Temperature	-13°F to +194°F (-25°C to +90°C)
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25.0m
	Weight (Metric)	7.78kg
	Weight (imperial)	17.1lbs