

166-90705

HellermannTyton

Article Number: 166-90705

Description: Liquid-Tight Metallic Conduit, Flexible, 0.75" (25mm) Dia, Galvanized Steel w/ Low Fire Hazard Cover, Black, 82ft/Reel



Base Data		
	Local Order Number	LTPLFH25B-25M
	Type	LTPLFH25B-25M
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL fittings. • Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance. • Smooth LFH cover resists oil and grease and possesses low fire hazard characteristics. • UV-resistant (black), suitable for outdoor use. • Halogen Free. • Manufactured to UL360 requirements.
	Quantity Per	reel
	Product Description	A flexible, liquid-tight galvanized steel conduit with a smooth, oil-resistant and low fire hazard cover. LTPLFH series is a general purpose, non-UL rated liquid-tight conduit used in applications that require movement, vibration and bending. Designed for applications within enclosed areas where limited smoke, low flame spread and low toxic gas emissions are required. Use with HelaGuard LTP or LTPUL Metallic Compression Fittings for IP66 + IP67 + IP68 + IP69 ratings. May be used in hazardous locations when accompanied with LTPUL or EXD metallic fittings.
	Technical Description	Manufacturer Reference Number: LTPLFH25B-25M
	Short Description	Liquid-Tight Metallic Conduit, Flexible, 0.75" (25mm) Dia, Galvanized Steel w/ Low Fire Hazard Cover, Black, 82ft/Reel
Product Dimensions		
	Length L (Imperial)	82.0ft
	Length L (Metric)	25.0m
	Reel Length (imperial)	82.0ft
	Diameter D (imperial)	0.83"
	Diameter D (metric)	21.0mm
	Outside Diameter D (imperial)	1.04"
	Outside Diameter OD (metric)	26.4mm
	Nominal Diameter (Imperial)	3/4"
	Nominal Diameter (Metric)	25mm

166-90705

HellermannTyton

Product Dimensions	Inside Bend Radius (Imperial)	5.12"
	Inside Bend Radius (Metric)	130mm
Material and Specifications		
	Material	Polyolefin (PO)
	Material Shortcut	PO
	Flammability	Self-Extinguishing according to EN IEC 61386-1
	Operating Temperature	-13°F to +194°F (-25°C to +90°C)
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25.0m
	Weight (imperial)	27.7lbs
	Weight (Metric)	12.58kg