

166-90707

HellermannTyton

Article Number: 166-90707

 Description: Liquid-Tight Metallic Conduit, Flexible, 0.38" (16mm) Dia,
Galvanized Steel w/TPE Cover, Black, 82ft/Reel


Base Data		
	Local Order Number	LTPHC16B-25M
	Type	LTPHC16B-25M
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL fittings. • Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance. • Smooth thermoplastic TPE-V rubber protects against corrosion remains flexible at low and high temperatures. • UV-resistant (black), suitable for outdoor use. • Manufactured to UL360 requirements. • Halogen free.
	Quantity Per	reel
	Product Description	A flexible, liquid-tight galvanized steel conduit with a smooth, halogen-free thermoplastic elastomer coating. LTPHC series is ideal for machinery or outdoor applications where extreme temperatures exist and liquid-tight performance is a requirement. Use with HelaGuard LTP or LTPUL Metallic Fittings for IP66 + IP67 + IP68 + IP69 ratings. May be used in hazardous locations when accompanied with LTPUL or EXD metallic fittings.
	Technical Description	Manufacturer Reference Number: LTPHC16B-25M
	Short Description	Liquid-Tight Metallic Conduit, Flexible, 0.38" (16mm) Dia, Galvanized Steel w/TPE Cover, Black, 82ft/Reel
Product Dimensions		
	Length L (Imperial)	82.0ft
	Length L (Metric)	25.0m
	Reel Length (imperial)	82.0ft
	Diameter D (imperial)	0.49"
	Diameter D (metric)	12.6mm
	Outside Diameter D (imperial)	0.70"
	Outside Diameter OD (metric)	17.8mm
	Nominal Diameter (Imperial)	3/8"
	Nominal Diameter (Metric)	16.0mm

166-90707



Product Dimensions	Inside Bend Radius (Metric)	45mm
Material and Specifications		
	Material	Thermoplastic Elastomer (TPE)
	Material Shortcut	GS
	Flammability	Self-Extinguishing according to EN IEC 61386-1
	Operating Temperature	-76°F to +302°F (-60°C to +150°C)
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25.0m
	Weight (imperial)	17.1lbs
	Weight (Metric)	7.78kg