

166-90711

HellermannTyton

Article Number: 166-90711

 Description: Liquid-Tight Metallic Conduit, Flexible, 1.25" (40mm) Dia,
Galvanized Steel w/TPE Cover, Black, 32.8 ft/Reel


Base Data		
	Local Order Number	LTPHC40B-10M
	Type	LTPHC40B-10M
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL fittings. • Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance. • Smooth thermoplastic TPE-V rubber protects against corrosion remains flexible at low and high temperatures. • UV-resistant (black), suitable for outdoor use. • Manufactured to UL360 requirements. • Halogen free.
	Quantity Per	reel
	Product Description	A flexible, liquid-tight galvanized steel conduit with a smooth, halogen-free thermoplastic elastomer coating. LTPHC series is ideal for machinery or outdoor applications where extreme temperatures exist and liquid-tight performance is a requirement. Use with HelaGuard LTP or LTPUL Metallic Fittings for IP66 + IP67 + IP68 + IP69 ratings. May be used in hazardous locations when accompanied with LTPUL or EXD metallic fittings.
	Technical Description	Manufacturer Reference Number: LTPHC40B-10M
	Short Description	Liquid-Tight Metallic Conduit, Flexible, 1.25" (40mm) Dia, Galvanized Steel w/TPE Cover, Black, 32.8 ft/Reel
Product Dimensions		
	Length L (Imperial)	32.8ft
	Length L (Metric)	10.0m
	Reel Length (imperial)	32.8ft
	Diameter D (imperial)	1.39"
	Diameter D (metric)	35.4mm
	Outside Diameter D (imperial)	1.65"
	Outside Diameter OD (metric)	41.8mm
	Nominal Diameter (Imperial)	1-1/4"
	Nominal Diameter (Metric)	40.0mm

166-90711



Product Dimensions	Inside Bend Radius (Metric)	175mm
Material and Specifications		
	Material	Thermoplastic Elastomer (TPE)
	Material Shortcut	TPE
	Flammability	Self-Extinguishing according to EN IEC 61386-1
	Operating Temperature	-76°F to +302°F (-60°C to +150°C)
Logistic and Packaging		
	Package Quantity (Imperial)	32.8ft
	Package Quantity (Metric)	10.0m
	Weight (imperial)	19.5lbs
	Weight (Metric)	8.85kg