

166-90716

# HellermannTyton

Article Number: 166-90716

Description: Liquid-Tight Metallic Conduit, Flexible, 0.50" (20mm) Dia, Galvanized Steel w/Halogen Free Polyurethane Cover, Black, 82ft/Reel



Base Data		
	Local Order Number	LTPPU20B-25M
	Type	LTPPU20B-25M
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL fittings.</li> <li>• Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance.</li> <li>• Polyurethane cover resists oil and will not crack or breakdown in low temperature applications.</li> <li>• Low fire hazard cover rated UL94 V0.</li> <li>• Manufactured to UL360 size requirements.</li> <li>• Halogen Free.</li> </ul>
	Quantity Per	reel
	Product Description	A flexible, liquid tight galvanized steel conduit with a smooth oil resistant polyurethane coating. LTPPU series is a halogen free conduit designed for low temperature performance, and has excellent flame retardation, limited smoke and low toxicity properties. Use with LTP or LTPUL series metallic fittings for IP66 + IP67 + IP68 + IP69 ratings. May be used in hazardous locations when accompanied with LTPUL or EXD metallic fittings.
	Technical Description	Manufacturer Reference Number: LTPPU20B-25M
	Short Description	Liquid-Tight Metallic Conduit, Flexible, 0.50" (20mm) Dia, Galvanized Steel w/Halogen Free Polyurethane Cover, Black, 82ft/Reel
Product Dimensions		
	Length L (Imperial)	82.0ft
	Length L (Metric)	25.0m
	Reel Length (imperial)	82.0ft
	Diameter D (imperial)	0.63"
	Diameter D (metric)	16.0mm
	Outside Diameter D (imperial)	0.83"
	Outside Diameter OD (metric)	21.1mm
	Nominal Diameter (Imperial)	1/2"
	Nominal Diameter (Metric)	20.0mm

166-90716



Product Dimensions	Inside Bend Radius (Metric)	65mm
Material and Specifications		
	Material	Polyurethane resin DS (PUR DS)
	Material Shortcut	PUR DS
	Flammability	UL 94 V0
	Operating Temperature	-40°F to +212°F (-40°C to +100°C)
Logistic and Packaging		
	Package Quantity (Imperial)	82ft
	Package Quantity (Metric)	25.0m
	Weight (Metric)	10.18kg
	Weight (imperial)	22.4lbs