

166-90721

Article Number: 166-90721

Description: Liquid-Tight Metallic Conduit, Flexible, 2" Dia (63mm), Galvanized Steel w/Halogen Free Polyurethane Cover, Black, 32.8 ft/Reel



Base Data	
Local Order Number	LTPPU63B-10M
Type	LTPPU63B-10M
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Flexible metallic conduit provides liquid-tight performance to IP66 + IP67 + IP68 + IP69 when used with LTP or LTPUL fittings. • Helically wound (spiral) galvanized steel core with an interlocking design delivers high degree of compression strength and impact resistance. • Polyurethane cover resists oil and will not crack or breakdown in low temperature applications. • Low fire hazard cover rated UL94 V0. • Manufactured to UL360 size requirements. • Halogen Free.
Quantity Per	reel
Product Description	A flexible, liquid tight galvanized steel conduit with a smooth oil resistant polyurethane coating. LTPPU series is a halogen free conduit designed for low temperature performance, and has excellent flame retardation, limited smoke and low toxicity properties. Use with LTP or LTPUL series metallic fittings for IP66 + IP67 + IP68 + IP69 ratings. May be used in hazardous locations when accompanied with LTPUL or EXD metallic fittings.
Technical Description	Manufacturer Reference Number: LTPPU63B-10M
Short Description	Liquid-Tight Metallic Conduit, Flexible, 2" Dia (63mm), Galvanized Steel w/Halogen Free Polyurethane Cover, Black, 32.8 ft/Reel
Product Dimensions	
Length L (Imperial)	32.8ft
Length L (Metric)	10.0m
Reel Length (imperial)	32.8ft
Diameter D (imperial)	2.03"
Diameter D (metric)	51.6mm
Outside Diameter D (imperial)	2.35"
Outside Diameter OD (metric)	59.7mm
Nominal Diameter (Imperial)	2-1/2"
Nominal Diameter (Metric)	63mm

166-90721



Product Dimensions	Inside Bend Radius (Metric)	280mm
Material and Specifications		
	Material	Galvanised Steel (GS)
	Material Shortcut	GS
	Flammability	UL 94 V0
	Operating Temperature	-40°F to +212°F (-40°C to +100°C)
Logistic and Packaging		
	Package Quantity (Imperial)	32.8ft
	Package Quantity (Metric)	10.0m
	Weight (Metric)	14.7kg
	Weight (imperial)	32.4lbs